




# Cavitation Solutions

*KO Anti-Cavitation Control Valves*

# Understanding Cavitation


When subjected to high-pressure differentials or high flow rates, valves often exhibit excessive noise and vibration. This is usually attributable to cavitation, which can eventually damage valves and related piping.



Cavitation occurs when the velocity of the fluid at the valve seating area becomes excessive, creating a sudden severe reduction in pressure that transforms the fluid into a vapor state, resulting in the formation of literally thousands of minute bubbles. The subsequent decrease in velocity and pressure rise that occurs after the valve seating area, when the pressurized condition resumes, causes these vapor bubbles to collapse at the rate of many times per second. Should this occur in close proximity to any metal surface, damage can take place. Over time, this can lead to valve failure.

#### **Cavitation's Damaging Effects**

- Excessive noise
- Erosion of valve body
- Damaged internal components
- Loss of flow capacity
- Pressure fluctuations
- Diminished performances
- High maintenance costs
- Valve failure
- Costly valve replacements




# Preventing Cavitation

## Cla-Val Cavitation Analysis Software

Understanding the circumstances under which cavitation noise and damage occurs in valves is critical to effectively operating and maintaining water distribution systems, particularly in those with high capacity operating requirements. To help achieve this understanding, Cla-Val offers Specifying Engineers and Maintenance Personnel a complete analysis of their distribution systems, utilizing our own in-house, state-of-the-art cavitation analysis software – CLA-CAV. Based on data and methodology developed by an independent test laboratory, the CLA-CAV program analyzes customer-provided parameters such as valve size, maximum and minimum flow rate, static/dynamic inlet and outlet pressure, typical water temperature and elevation above sea level to accurately predict if and when a valve will experience critical, damaging or choking cavitation. Armed with this data, our application specialists can advise which valve or valve combination will be best suited to handle a given system's flow control requirements.

### The CLA-CAV Advantage

- CLA-CAV identifies when damaging cavitation will occur in addition to the onset of critical cavitation.
- CLA-CAV helps to identify which valve or equipment combination will be the most effective means to eliminate potential cavitation damage.
- CLA-CAV helps to lower system maintenance costs by predicting cavitation damage before it happens.



Visit [www.cla-val.com](http://www.cla-val.com) to download technical data sheets for the 100-01 KO Anti-Cavitation Valve.

### For Engineers

Utilizing the CLA-CAV cavitation analysis program is an important first step in designing a water distribution system that will withstand the extreme conditions of high pressure drops and flow rates, while helping to ensure long, trouble-free operation of your control valves and the system as a whole.

### For Operators

In many cases, installing Cla-Val's anti-cavitation valve or retrofitting an existing valve with anti-cavitation trim will be the preferred method to eliminate the potential for noise and damage. In other scenarios, our experts may make alternate recommendations such as multiple valves installed in series as the most cost-effective means to combat cavitation while providing optimum performance.



# Model 100-01KO & 100-01KO-1 Anti-Cavitation Valves


## KO Anti-Cavitation Trim



Cla-Val's KO anti-cavitation trim represents a dramatic departure from the standard approaches usually employed to fight cavitation in valves that are required to undergo extreme pressure differentials and high velocity flow conditions capable of pressure differentials up to 150psid.

Constructed of 316 Stainless Steel, the seat and disc guide feature dual interlocked sleeves containing cast radial slots that deflect internal flow to impinge upon itself, harmlessly dissipating potential noise and cavitation damage. The cast radial slots create a larger flow path than is possible with the standard drilled holes typically employed by other anti-cavitation valves currently available in the market place. The uniquely designed radial slots in the seat and disc guides also lessen the possibility of fouling if small particles are present in the water.

## KO-1 Anti-Cavitation Trim



The Cla-Val Model KO-1 Anti-Cavitation Trim is ideal for high differential applications requiring remote control, pressure regulation, solenoid operation, rate of flow control, or level control, capable of serving pressure differentials up to 300psid.


This model provides optimum internal pressure control through a unique anti-cavitation trim design. Constructed of 316 Stainless Steel, the seat and disc guide trim components feature dual interlocking sleeves. The seat contains variable flow apertures followed by a deflected to maximum pressure drop through the seat at low valve positions. As the valve position increases, the flow area increases through the seat, maximizing the flow through the valve. The seat center hole feature allows additional flow capacity through the valve at higher valve positions. The disc guide features radial slots that deflect internal flow to impinge upon itself in the center of the flow path, harmlessly dissipating the potential for cavitation damage. The KO-1 components can be retrofitted.

# Model 100-01KO & 100-01KO-1 Anti-Cavitation Valves


Seat with Radial Slots

Slotted Disc Guide

Seat with Variable Flow Apertures



KO Trim




KO-1 Trim

## Typical Applications

- Pressure Reducing Valve Stations
- Tank Fill Valve Applications
- Noise Reduction in High-Rise Building Valve Stations
- Reservoir Level Control Valve Applications
- Booster Pump Bypass Stations
- Offshore Fire Pump Relief Valve Protection
- Applications with discharge to atmosphere
- Any application where valves are subjected to extreme pressure differentials or high velocity flow conditions

# Model 100-01KO & 100-01KO-1 Anti-Cavitation Valves

## Three Stages of Pressure Reduction



1

Flow enters through the seat.

2

Flow impinges upon itself within the seat and disc guide assembly to dissipate cavitation and further reduce pressure.

3

Flow exits through the disc guide for final pressure reduction. Diagonal disc guide slots direct flow away from surfaces.

TRUSTED FOR  
GENERATIONS  
INNOVATING  
FOR **TOMORROW**



# Global Locations



## Global Headquarters

1701 Placentia Avenue  
Costa Mesa, CA 92627  
949-722-4800  
800-942-6326  
info@cla-val.com  
www.cla.val.com

**Western USA**  
800-942-6326

**Central USA**  
800-533-8181

**Eastern USA**  
800-451-3030

**Cla-Val Canada**  
905-563-4963  
sales@cla-val.ca

## Cla-Val Latin America

52-(33)-80007565  
info@cla-val.com  
www.cla-val-latinamerica.com

## Cla-Val Europe

Chemin Des Mesanges 1  
CH-1032 Romanel/Lausanne  
Switzerland  
41-21-643-15-55  
cla-val@cla-val.ch

## Cla-Val United Kingdom

44-1892-514-400  
info@cla-val.co.uk

## Cla-Val France

33-4-72-25-92-93  
cla-val@cla-val.fr

## Cla-Val Asia Pacific

+ 64-3-9644860  
info@cla-valpacific.com  
www.cla-valpacific.com

## Cla-Val UAE

+ 971 4 5667665  
cla-val@cla-val.ch

## Cla-Val Singapore

+65 91798177  
wktan@cla-val.com

## Cla-Val China

info@cla-valpacific.com